



# IT power distribution module 3 pole 5 wire 16A - IEC309 1040cm

PDM3516IEC-1040

Price: 12,776.27 ZAR

#### **Overview**

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead Time	Usually Ships within 3 Weeks

#### Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V 400 V 3 phases
Provided Equipment	Installation guide

### **Physical**

Colour	Grey
Height	15.2 cm
Width	43.2 cm
Depth	40.6 cm
Net Weight	4.29 kg

## Input

Network Frequency	50 Hz
Max Line Current	16 A

### **Output**

Max Current Draw	16 A
Number Of Power Socket Outlets	1 IEC 309 16 A

#### Conformance

Product Certifications	CE
	VDE

## **Packing Units**

19 Apr 2024

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	40.6 cm

Package 1 Length	43.2 cm
Package 1 Weight	5.2 kg

## **Contractual warranty**

Warranty 1 year repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

#### Resource performance



Take-Back Program Available

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information