





Usually in Stock

Lead-acid battery

Documentation CD User manual USB cable

APC Easy UPS 1 Ph Line Interactive, 3kVA, Tower, 230V, 6 Universal outlets, AVR, LCD

SMV3000AI-MS

Overview

Lead Time

Battery Type

Provided Equipment

	·	
Main		
Main Input Voltage	230 V	
Input Voltage	220 V 240 V	
Main Output Voltage	230 V	
Rated Power In W	2100 W	
Rated Power In Va	3000 VA	
Product Or Component Type	Uninterruptible power supply (UPS)	
Input Connection Type	IEC 60320 C20	
Output Connection Type	6 universal receptacle	
Number Of Cables	1	

Batteries & Runtime

Run Time	View Runtime Graph ☐	
Efficiency	View Efficiency Graph ☐	
Number Of Battery Filled Slots	0	
Number Of Battery Free Slots	0	
Battery Recharge Time	4 h	
Battery Voltage	48 V	
Battery Charger Power	99 W rated	
Battery Life	35 year(s)	
Replacement Battery	APCRBCV209 ☐	
Extended Runtime	0	

General

Number Of Power Module Free Slots	0
Number Of Power Module Filled	0

Redundant	No
Ups Size	WS

Physical

Colour	Black	
Height	24 cm	
Width	18 cm	
Depth	45.5 cm	
Net Weight	25.2 kg	
Mounting Preference	No preference	
Mounting Mode	Not rack-mountable	
Two Post Mountable	0	
Usb Compatible	No	

Input

Network Frequency	4565 Hz +/- 1 Hz auto-sensing
Input Voltage Limits	165295 V

Output

Maximum Configurable Power In W	2100 W	
Output Frequency	50/60 Hz +/- 1 Hz unsynchronised	
Crest Factor	3:1	
Ups Type	Line interactive	
Wave Type	Sine wave	
Graph Display	1	
Maximum Configurable Power In Va	3000 VA	
Transfer Time	2-6 ms typical : 12 ms maximum	

Conformance

Product Certifications	CE
	TICI

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	03000 m
Ambient Air Temperature For Storage	-1040 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	015000 m
Acoustic Level	45 dBA
Ip Degree Of Protection	IP20

Communications & Management

Alarm

Alarm when on battery : distinctive low battery alarm : overload continuous tone

Surge Protection and Filtering

Surge Energy Rate

125 J

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	41.05 cm
Package 1 Width	31.9 cm
Package 1 Length	60.1 cm
Package 1 Weight	28.9 kg

Contractual warranty

Warranty

2 years repair or replace

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information