



EcoStruxure Operator Terminal Expert Runtime, Email

HMIRTW CZLSPA ZZ

EAN Code: 3606489508357

Prijs: 330,25 EUR

Hoofd

Range Of Product	Ecostruxure operator terminal Expert
Product Or Component Type	Licentie
Formaat	Digitaal
Type Licentie	Licentie vergrendeld knooppunt
Variant	Runtime
Softwareversie	V3.5
Operating System Requirement	Windows 10 64 bit
Systeemvereisten	8 GB RAM 30 GB ruimte op harde schijf
Taal	Engels Italiaans Chinees Spaans Frans Duits Portugees Koreaans

Complementair

Licentiecategorie	Permanent
-------------------	-----------

De weergegeven prijs is de adviesprijs in euro excl. BTW. Deze kan onderhevig zijn aan korting. Neem contact op met uw lokale distributeur of detailhandel voor de daadwerkelijke prijs

Disclaimer: Deze documentatie is niet bedoeld als vervanging voor en mag niet worden gebruikt voor het bepalen van de geschiktheid of betrouwbaarheid van deze producten voor specifieke gebruikerstoepassingen

Protocol Communicatiepoort	CANopen slave Couzet Automation millenium 3 FBD Emerson Industrial Automation Modbus SIO master Control Techniques Modbus SIO master Emerson Process Management ROC Plus Ethernet Emerson Process Management ROC SIO HTTP IPsec Mitsubishi A Series Ethernet Mitsubishi FX series CPU direct Mitsubishi FX series Ethernet Mitsubishi iQ-R/F series Ethernet SLMP client Mitsubishi Q series CPU direct Mitsubishi Q series QnU CPU Ethernet Mitsubishi Q/QnA series serial Modbus Organization Modbus SIO ASCII master Modbus Organization Modbus SIO master Modbus Organization Modbus SIO slave Modbus Organization Modbus TCP master Modbus Organization Modbus TCP slave Omron CS/CJ/CP series host link Omron CS/CJ/CP/NX series Ethernet Omron CS/CJ/NJ/NX series Ethernet/IP OPC UA server Profibus DP slave Rockwell Automation Ethernet/IP Rockwell Automation DF1 Rockwell Automation DH485 Schneider Electric Modbus SIO master Schneider Electric Modbus TCP master Schneider Electric Modbus TCP master via USB Schneider Electric Machine expert network Schneider Electric PacDrive Schneider Electric Uni-Telway Schneider Electric Zelio Logic Siemens Simatic S7 Ethernet Siemens Simatic S7 MPI direct Siemens TIA portal Ethernet websocket
Vorige Software-Versie	V3.4
Softwarefunctie	Alarms and events Blocky script Convertors Import export with CSV, tab and period delimiter Data and operation logging Multi language development Multi language tables Object binding and properties Target binding and properties Project transfer (Ethernet, filesystem, USB cable) Recipes Screens (contents and folders) Security (levels, project, users) Project and application settings System keypad Text script Color themes Variable (arrays, binding, properties, structures) OPC UA server Web server API
Bereik Compatibiliteit	Harmony GTU Harmony GTUX Harmony ST6 Harmony STM6 Harmony STO7 Harmony iPC
Hosting Optie	On-device
Licentiegrootte	Single (1 station)
Processor Requirement	Intel core i3 8th generation Intel core i5 8th generation
Resolutie Display	320 x 240 pixels HVGA minimum 3840 x 2160 pixels 4K UHD maximum

