Product data sheet

Specifications





500 V

White

10 mm

1 N.m

Auxiliary contact, Acti9, iOF/ SD+OF, 2OC, AC/DC

A9A26929

! Discontinued on: 30/08/2023

! Discontinued

Main

Range Of Product	Acti9
Product Or Component Type	Double OC or fault contact
Device Short Name	iOF/SD+OF
Signal Contacts Composition	2 C/O
[In] Rated Current	DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC
	DC-12 1.5 A at 48 V, DC
	DC-12 6 A at 24 V, DC
	AC-12 3 A at 415 V, AC 50/60 Hz
	AC-12 6 A at 240 V, AC 50/60 Hz
9 Mm Pitches	1

Complementary

[Ui] Rated Insulation Voltage

[Uimp] Rated Impulse Withstand Voltage	4 kV
Local Signalling	Mechanical indicator
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
Height	90 mm
Width	9 mm
Depth	73 mm
Net Weight	43 g

Screw clamp terminal (top and bottom) 2 cable(s) 2.5 mm² - rigid

Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm 2 - flexible with ferrule Screw clamp terminal (top and bottom) 1 cable(s) 0.5...2.5 mm 2 - flexible Screw clamp terminal (top and bottom) 1 cable(s) 1...4 mm 2 - rigid

Environment

Connections - Terminals

Wire Stripping Length

Tightening Torque

Colour

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1

Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	2.400 cm
Package 1 Length	9.200 cm
Package 1 Weight	50.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	27.000 cm
Package 2 Weight	693.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	7.600 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information