# Product data sheet

Specifications

#### Green Premium<sup>™</sup>



### impulse relay iTL - 2P - 2 NO -16A - coil 130 VAC 50/60Hz- 48 VDC

A9C30312

#### Main

Range Of Product	Acti9
Product Name	Acti9 iTL
Product Or Component Type	Impulse relay
Device Short Name	iTL
Device Application	Standard
Poles	2P
Pole Contact Composition	2 NO
[In] Rated Current	16 A
Network Type	AC
[Uc] Control Circuit Voltage	130 V AC 50/60 Hz 48 V DC

### Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
Control Type	Remote and manual control Coil deconnection
Control Signal Type	Impulse
Switching Frequency	5 switching operations/minute 100 switching operations/day
Impulse Duration	50 ms1 s
Remote Control Type	Illuminated push-button 3 mA
Local Signalling	ON/OFF indication
Mounting Mode	Fixed
Mounting Support	DIN rail
9 Mm Pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Electrical Durability	AC-21: 200000 cycles AC-22: 100000 cycles

Connections - Terminals	Control circuit: tunnel type terminals 1 cable(s) 0.54 mm <sup>2</sup> rigid Control circuit: tunnel type terminals 1 cable(s) 0.54 mm <sup>2</sup> rigid with cable end Control circuit: tunnel type terminals 1 cable(s) 14 mm <sup>2</sup> flexible Control circuit: tunnel type terminals 1 cable(s) 14 mm <sup>2</sup> flexible with ferrule Power circuit: tunnel type terminals 1 cable(s) 1.54 mm <sup>2</sup> rigid Power circuit: tunnel type terminals 1 cable(s) 1.54 mm <sup>2</sup> rigid with cable end Power circuit: tunnel type terminals 1 cable(s) 1.54 mm <sup>2</sup> rigid with cable end Power circuit: tunnel type terminals 1 cable(s) 1.54 mm <sup>2</sup> flexible Power circuit: tunnel type terminals 1 cable(s) 1.54 mm <sup>2</sup> flexible
Wire Stripping Length	11 mm
Tightening Torque	1 N.m
Range Compatibility	Acti 9 iATEt Acti 9 iATLc Acti 9 iATLc+s Acti 9 iATLm

Acti 9 iATLs Acti 9 iETL iTL 16 Acti 9 iATLc+c

### Environment

Standards	EN 669-1 EN 669-2-2
	LN 003-2-2
Product Certifications	GOST
Quality Labels	NF
-	VDE
	CEBEC
	КЕМА
	IMQ
Noise Level	60 dB
Ip Degree Of Protection	IP20 conforming to IEC 60529 (on opening)
	IP40 conforming to IEC 60529 (in enclosure)
Pollution Degree	3
- · · ·	
Tropicalisation	2
Relative Humidity	95 % at 55 °C
	00 50.00
Ambient Air Temperature For Operation	-2050 °C
Ambient Air Temperature For	-4070 °C
Storage	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7.0 cm
Package 1 Length	8.5 cm
Package 1 Weight	112.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.0 cm
Package 2 Width	9.0 cm
Package 2 Length	23.0 cm
Package 2 Weight	1.396 kg
Unit Type Of Package 3	S03

Number Of Units In Package 3	144
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	17.239 kg

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations