# **Product data sheet**

Specifications





# switch disconnector iSW - 3P - 40 A - 415 V

A9S66340

### Main

Range	Acti9	
Product Name	Acti9 iSW	
Product Or Component Type	Switch disconnector	
Device Short Name	iSW	
Device Application	Isolation Control	
Poles Description	3P	
Utilisation Category	AC-22A	
Suitability For Isolation	Yes	

# Complementary

[le] Rated Operational Current	40 A at 415 V AC 50/60 Hz
[Ue] Rated Operational Voltage	415 V AC 50/60 Hz
[Icm] Rated Short-Circuit Making Capacity	5 kA switch-disconnector alone
[Icw] Rated Short-Time Withstand Current	1260 A
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
Control Type	Toggle
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top or bottom: YES
9 Mm Pitches	6
Height	85 mm
Width	54 mm
Depth	73 mm
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	15000 cycles

Connections - Terminals	Tunnel type terminals (top or bottom) - <= $1 \times 50 \text{ mm}^2$ - rigid  Tunnel type terminals (top or bottom) - <= $1 \times 35 \text{ mm}^2$ - flexible  Tunnel type terminals (top or bottom) - <= $1 \times 35 \text{ mm}^2$ - flexible with ferrule
Wire Stripping Length	14 mm
Tightening Torque	3.5 N.m

## **Environment**

Standards	EN 60947-3 AS 60947-3 BS EN 60947-3 IEC 60947-3 NZS 60947-3
Ip Degree Of Protection	IP20
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4085 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.85 cm
Package 1 Width	5.4 cm
Package 1 Length	9.2 cm
Package 1 Weight	264.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	8.0 cm
Package 2 Width	9.0 cm
Package 2 Length	22.0 cm
Package 2 Weight	1.106 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	44
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	12.653 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations