Product data sheet





56 Series, Auxillary Switch Contact, 0.1A 125V Gold Plate IP66, Suits 56SW350/2

PDL56SW01

! Discontinued on: 17/08/2023

! Discontinued

Main

Range Of Product	56 Series™
Product Or Component Type	Auxiliary contact
Control Type	Rotary

Complementary

Material	PC (polycarbonate)
Contacts Material	Gold plated
Colour Tint	White
Surface Finish	Gloss
Rated Current	0.05 A 0.1 A
[Ue] Rated Operational Voltage	125 V 250 V
Network Frequency	50 Hz
Network Number Of Phases	1 phase
Number Of Gangs	1 gang
Number Of Poles	1
Mounting Mode	Surface mounted
Ambient Air Temperature For Operation	-4055 °C
Auxiliary Contact Composition	1 NO/NC
Quantity Per Set	Set of 5
Type Of Packing	Carton

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.014 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations