

# Product data sheet

Specifications



## 15A 250V - triple phase 3 pole - round pin - IP66 (grey)

S56SO315RPGY

### Main

Range	WPS
Device short name	56 series
Product or component type	Socket-outlet
Colour tint	Light grey

### Complementary

Material	PVC (polyvinyl chloride) UV stabilised
Surface finish	Gloss
Width	101 mm
Height	107 mm
Depth	77 mm
Rated current	15 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	3 phases
Number of gangs	1 gang
Pin number	3
Device composition	Round pin
Mounting mode	Surface mounted

### Environment

IP degree of protection	IP66
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	10.4 cm
Package 1 Length	10.5 cm
Package 1 Weight	500.0 g

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>RoHS exemption information</b>	Yes
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Recommended replacement(s)