

Product data sheet

Specifications



32A 250V - triple phase 3 pole - round pin - IP66 (grey)

S56SO332GY

Main

Range	WPS
Device short name	56 series
Product or component type	Socket-outlet
Colour tint	Light grey

Complementary

Material	PVC (polyvinyl chloride) UV stabilised
Surface finish	Gloss
Width	101 mm
Height	107 mm
Depth	102 mm
Rated current	32 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	3 phases
Number of gangs	1 gang
Pin number	3
Device composition	Round pin
Mounting mode	Surface mounted

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	10.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	500.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Recommended replacement(s)