

# Product data sheet

Specifications



## modular single phase power meter ME1 - 230V - 0..63A

17065

 **Discontinued on:** Dec 31, 2012

 **Discontinued**

### Main

Range	PowerLogic
Range Of Product	ME
Device Short Name	ME1
Product Or Component Type	Active energy hour meter

### Complementary

Poles Description	1P + N
Type Of Measurement	Active power
Device Application	Sub billing
Accuracy Class	Class 1 active energy conforming to IEC 62053-21
Input Type	Direct input
[In] Rated Current	63 A
Rated Voltage	230 V +/- 20 %
Network Frequency	60 Hz 50 Hz
Technology Type	Electronic
Display Type	LCD display
Maximum Value Measured	999.99 MWh
Local Signalling	Yellow indicator light: metering and activity
Power Consumption In Va	2.5 VA
Mounting Mode	Clip-on
Mounting Support	DIN rail
Connections - Terminals	Tunnel type terminals16 mm² bottom Tunnel type terminals6 mm² top
Standards	IEC 61036

### Environment

Ip Degree Of Protection	Front face: IP40
9 Mm Pitches	4
Width	36 mm
Height	81 mm

List Price displayed is VAT EXCLUSIVE.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	65 mm
-------	-------

## Contractual warranty

Warranty	18 months
----------	-----------