


Price* : 2,079.46 PHP



⚠ Discontinued

Main

Range	Vivace
Product or component type	Cooker control unit socket
Device short name	KBT15
Device application	Power supply
Device presentation	Complete mechanism
Switch application	Cooker and socket

Complementary

Pilot light	Red neon indicator
Outlet poles configuration	2P + E
Colour tint	Aluminium silver
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	120.6 mm
Embedding depth	47 mm
Rated current	45 A at 250 V AC, resistive 45 A at 250 V AC, inductive
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	Earth L N
Tightening torque	0.4 N.m
Clamping connection capacity	<= 16 mm ²
Width	146 mm

* List Price displayed is VAT EXCLUSIVE.

Height	86 mm
--------	-------

Environment

Standards	BS 4177
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Packing Units

Package 1 Weight	165.280 g
Package 1 Height	86.000 mm
Package 1 width	36.000 mm
Package 1 Length	146.000 mm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
