# **Product data sheet**

Specifications





## Power Dist. Mod. 3x1 POLE 3 Wire RCD 32A 3xIEC309 480CM, 540CM, 600CM

PDM2332IEC-3P30R-2

_		•	
( )\	/er	V16	эw

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead Time	Usually Ships within 4 Weeks

#### Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V
Provided Equipment	Installation guide

## **Physical**

Colour	Grey
Height	25.4 cm
Width	43.2 cm
Depth	40.6 cm
Net Weight	9.5 kg

## Input

Network Frequency	50 Hz
Max Line Current	32 A

#### **Output**

Max Current Draw	32 A
Number Of Power Socket Outlets	3 IEC 309 32 A

#### **Conformance**

Product Certifications	CE
	VDE

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.4 cm
Package 1 Width	40.6 cm

List Price displayed is VAT EXCLUSIVE.



Package 1 Length	43.2 cm	
Package 1 Weight	10.4 kg	



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

#### Resource performance



Take-Back Program Available

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information