



Price\* : 497.32 PHP



## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC 120 V AC 48 V DC
Mounting Type	Bolt-on
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR and Switching Duty rated
Electrical Connection	Pressure plate

## Complementary

Interrupt Rating	10 kA at 120/240 V AC 50/60 Hz 10 kA at 120 V AC 50/60 Hz 5 kA at 48 V DC
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	5 N.m for 10...25 mm <sup>2</sup> (AWG 8...AWG 2)
Height	76.20 mm
Width	19.05 mm
Depth	73.91 mm

## Environment

Certifications	UL listed CSA
Ambient Rating	40 °C

\* List Price displayed is VAT EXCLUSIVE.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	127 g
Package 1 Height	8.382 cm
Package 1 width	2.032 cm
Package 1 Length	8.636 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.293 kg
Package 2 Height	8.382 cm
Package 2 width	2.032 cm
Package 2 Length	19.812 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	13.177 kg
Package 3 Height	20.32 cm
Package 3 width	20.066 cm
Package 3 Length	43.434 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------