



Osnovne informacije

Opseg	Prisma
Kompatibilnost grupe proizvoda	Prisma G
Tip proizvoda ili komponente	Montažna ploča
Pribor / posebna kategorija	Instalacioni pribor
Instalirani uređaji	Compact : fixed NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation Compact : fixed NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation Easypact : fixed CVS400 without earth leakage protection - control: direct front rotary handle - vertical installation Easypact : fixed CVS630 without earth leakage protection - control: direct front rotary handle - vertical installation Compact : fixed NSX400 with earth leakage protection - control: direct front rotary handle - vertical installation Compact : fixed NSX630 with earth leakage protection - control: direct front rotary handle - vertical installation Easypact : fixed CVS400 with earth leakage protection - control: direct front rotary handle - vertical installation Easypact : fixed CVS630 with earth leakage protection - control: direct front rotary handle - vertical installation
Opis polova	1 x 3P : fixed : NSX400 vertical installation 1 x 3P : fixed : NSX630 vertical installation 1 x 3P : fixed : CVS400 vertical installation 1 x 3P : fixed : CVS630 vertical installation 1 x 4P : fixed : NSX400 vertical installation 1 x 4P : fixed : NSX630 vertical installation 1 x 4P : fixed : CVS400 vertical installation 1 x 4P : fixed : CVS630 vertical installation

Dopunske informacije

Opis instalacije	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Broj vertikalnih modula (50 mm)	15 module(s) : CVS400 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)

15 module(s) : CVS400 without earth leakage protection , direct with long terminal shield in 600 mm
Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
15 module(s) : CVS630 without earth leakage protection , direct with long terminal shield in 600 mm
Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
15 module(s) : CVS630 without earth leakage protection , direct with long terminal shield in 600 mm
Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
15 module(s) : NSX400 without earth leakage protection , direct with long terminal shield in 600 mm
Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
15 module(s) : NSX400 without earth leakage protection , direct with long terminal shield in 600 mm
Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
15 module(s) : NSX630 without earth leakage protection , direct with long terminal shield in 600 mm
Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
15 module(s) : NSX630 without earth leakage protection , direct with long terminal shield in 600 mm
Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
18 module(s) : CVS400 with earth leakage protection , direct with long terminal shield in 600 mm
Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
18 module(s) : CVS400 with earth leakage protection , direct with long terminal shield in 600 mm
Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
18 module(s) : CVS630 with earth leakage protection , direct with long terminal shield in 600 mm
Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
18 module(s) : CVS630 with earth leakage protection , direct with long terminal shield in 600 mm
Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
18 module(s) : NSX400 with earth leakage protection , direct with long terminal shield in 600 mm
Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
18 module(s) : NSX400 with earth leakage protection , direct with long terminal shield in 600 mm
Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
18 module(s) : NSX630 with earth leakage protection , direct with long terminal shield in 600 mm
Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
18 module(s) : NSX630 with earth leakage protection , direct with long terminal shield in 600 mm
Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)

Uslovi upotrebe	Need additional plate (1M high) when installation of device is in vertical
Visina	500 mm
Masa proizvoda	2.24 kg
Završna obrada	Mat Glatko
Tretman zaštite	Elektroforeza i vruće polimerizovan poliesterski epoksi prah
Boja	Bela RAL 9001

Okruženje

Standardi	IEC 61439-2
Sertifikacija proizvoda	ASEFA

Održivost ponude

Održiva oprema - status	Zeleni Premium proizvod
RoHS (kod datuma: GGNN)	Usaglašeno - od 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Referenca ne sadrži SVHC iznad propisanog praga Referenca ne sadrži SVHC iznad propisanog praga
Profil proizvoda u odnosu na životnu sredinu	Dostupno Profil ekološke prihvatljivosti proizvoda
Instrukcije za kraj životnog veka proizvoda	Nisu potrebne posebne operacije za reciklažu

Ugovorna garancija

Garantni period	18 meseci
-----------------	-----------