



Osnovne informacije

Opseg	Prisma
Kompatibilnost grupe proizvoda	Prisma G
Tip proizvoda ili komponente	Prednja ploča
Pribor / posebna kategorija	Instalacioni pribor
Tip prednje ploče	Otvor
Instalirani uređaji	Compact : fixed INS250 - control: direct front rotary handle - horizontal installation Compact : fixed INV250 - control: direct front rotary handle - horizontal installation Compact : fixed INV100 - control: direct front rotary handle - horizontal installation Compact : fixed INV160 - control: direct front rotary handle - horizontal installation Compact : fixed INV200 - control: direct front rotary handle - horizontal installation
Opis polova	1 x 3P : mounting plate support : INS250 horizontal installation 1 x 4P : mounting plate support : INS250 horizontal installation 1 x 3P : mounting plate support : INV100 horizontal installation 1 x 4P : mounting plate support : INV100 horizontal installation 1 x 3P : mounting plate support : INV160 horizontal installation 1 x 4P : mounting plate support : INV160 horizontal installation 1 x 3P : mounting plate support : INV200 horizontal installation 1 x 4P : mounting plate support : INV200 horizontal installation 1 x 3P : mounting plate support : INV250 horizontal installation 1 x 4P : mounting plate support : INV250 horizontal installation
Radni položaj	Horizontalna

Dopunske informacije

Opis kućišta/ormana	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Pozicija priključka	Direktno povezivanje Povezivanje bloka
Broj vertikalnih modula (50 mm)	4
Standardi	IEC 61439-2 IEC 61439-1
Sertifikacija proizvoda	ASEFA

Količina po setu	Set od 1
Visina	200 mm
Širina	500 mm
Masa proizvoda	0.8 kg
Materijal	Čelik
Završna obrada	Mat Glatko
Tretman zaštite	Elektroforeza i vruće polimerizovan poliesterski epoksi prah
Boja	Bela RAL 9001

Okruženje

IK stepen zaštite	IK07 conforming to EN/IEC 62262
-------------------	---------------------------------

Održivost ponude

Održiva oprema - status	Zeleni Premium proizvod
RoHS (kod datuma: GGNN)	Usaglašeno - od 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Referenca ne sadrži SVHC iznad propisanog praga Referenca ne sadrži SVHC iznad propisanog praga
Profil proizvoda u odnosu na životnu sredinu	Dostupno Profil ekološke prihvatljivosti proizvoda
Instrukcije za kraj životnog veka proizvoda	Nisu potrebne posebne operacije za reciklažu

Ugovorna garancija

Garantni period	18 meseci
-----------------	-----------