

Lista sa podacima o proizvodima

Specifikacije



IP30 ventilaciona poklopna ploča Š600/650 3M



03895

! Obustavljeno: 28. 3. 2022.

! Discontinued

Osnovne informacije

Grupa Proizvoda	Prisma
Grupa Proizvoda	Prisma G Prisma P
Tip Proizvoda Ili Komponente	Prednja ploča
Pribor / Posebna Kategorija	Instalacioni pribor
Kompatibilnost Grupe Proizvoda	Prisma Prisma G orman Prisma Prisma P kućište
Tip Prednje Ploče	Za ventilaciju

Dopunske informacije

Opis Kućišta/Ormana	Slobodnostojeći orman - širina 600 mm Nadzidni orman - širina 600 mm Kućište - širina 650 mm dubina 400 mm Pack orman - širina 555 mm
Broj Vertikalnih Modula (50 Mm)	3
Standardi	IEC 61439-2 IEC 61439-1
Sertifikacija Proizvoda	ASEFA
Materijal	Čelik
Završna Obrada	Mat Glatko
Tretman Zaštite	Elektroforeza i vruće polimerizovan poliesterski epoksi prah
Boja	Bela (RAL 9001)
Visina	150 mm
Širina	500 mm
Masa Proizvoda	0,46 kg
Količina Po Setu	Set od 1
Functional Unit	600 mm Prisma G slobodnostojeći orman 600 mm Prisma G nadzidni orman 650 mm 400 mm Prisma P kućište

Okruženje

Ip Stepen Zaštite	IP30
-------------------	------

Pakovanje

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3,0 cm
Package 1 Width	15,0 cm
Package 1 Length	50,0 cm
Package 1 Weight	493,0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	15,5 cm
Package 2 Width	22,0 cm
Package 2 Length	81,5 cm
Package 2 Weight	5,839 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	120
Package 3 Height	105,0 cm
Package 3 Width	80,0 cm
Package 3 Length	120,0 cm
Package 3 Weight	60,24 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti

- ✓

Reach Bez Svhc
- ✓

Bez Toksičnih Teških Metala
- ✓

Bez Žive
- ✓

Informacije O Rohs Izuzecima

Da
- ✓

Proizvod Sa Plastičnim Delovima Bez Halogena

Sertifikacija i standardi

Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu Proaktivna RoHS deklaracija za Kinu (izvan RoHS pravnog okvira za Kinu)
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda