



Osnovne informacije

Opseg	Linergy
Ime proizvoda	Linergy DX
Tip proizvoda ili komponente	Fleksibilno povezivanje
Pribor / posebna kategorija	Pribor za razvod struje
Kompatibilnost proizvoda	NG125

Dopunske informacije

Veza kućišta i uređaja	Linergy DX distribution block
Opis instalacije	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure - width 600 mm Cubicle - width 800 mm Pack enclosure - width 555 mm
Instalirani uređaji	Multi 9 : fixed NG125 with earth leakage protection - control: toggle Multi 9 : fixed NG125 without earth leakage protection - control: toggle Multi 9 : fixed NG125 NA - control: toggle Acti 9 : fixed C120 with earth leakage protection - control: toggle Acti 9 : fixed C120 without earth leakage protection - control: toggle Compact : fixed NG160 with earth leakage protection - control: toggle Compact : fixed NG160 without earth leakage protection - control: toggle Compact : fixed NG160 NA without earth leakage protection - control: toggle Acti 9 : fixed iC120 with earth leakage protection - control: toggle Acti 9 : fixed iC120 without earth leakage protection - control: toggle Compact : fixed INS40 - control: direct front rotary handle vertical installation Compact : fixed INS63 - control: direct front rotary handle vertical installation Compact : fixed INS100 - control: direct front rotary handle vertical installation Compact : fixed INS125 - control: direct front rotary handle vertical installation Compact : fixed INS160 - control: direct front rotary handle vertical installation Compact : fixed NSXm without earth leakage protection - control: toggle vertical installation Compact : fixed NSXm with earth leakage protection - control: toggle vertical installation
Uslovi upotrebe	Additional connector needed for INS40...160 (to be ordered separately)
Maksimalna [Ie] nazivna radna struja	125 A

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Količina po setu	Set od 4
Dužina	240 mm
Masa proizvoda	0.52 kg

Okruženje

Standardi	IEC 61439-2 IEC 61439-1
Sertifikacija proizvoda	ASEFA

Održivost ponude

Održiva oprema - status	Zeleni Premium proizvod
RoHS (kod datuma: GGNN)	Usaglašeno - od 0707 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Referenca ne sadrži SVHC iznad propisanog praga Referenca ne sadrži SVHC iznad propisanog praga
Profil proizvoda u odnosu na životnu sredinu	Dostupno Profil ekološke prihvatljivosti proizvoda
Instrukcije za kraj životnog veka proizvoda	Nisu potrebne posebne operacije za reciklažu

Ugovorna garancija

Garantni period	18 meseci
-----------------	-----------