

# Lista sa podacima o proizvodima

Specifikacije



modularni sigurnosni transformator  
iTR - 230 V 50..60 Hz -izlaz 12..24 V  
- 63 VA

A9A15222

Cena\* bez PDV-a: 7.545,00 RSD

## Osnovne informacije

|                              |                          |
|------------------------------|--------------------------|
| Tip Transformatora           | Sigurnosni transformator |
| Grupa Proizvoda              | Acti9                    |
| Grupa Proizvoda              | Acti 9                   |
| Ime Proizvoda                | Acti 9 iTR               |
| Tip Proizvoda Ili Komponente | Transformator            |
| Kratko Ime Uređaja           | iTR                      |

## Dopunske informacije

|                                 |                                                                                   |
|---------------------------------|-----------------------------------------------------------------------------------|
| [Ue] Nazivni Napon              | 230 V AC 50/60 Hz                                                                 |
| Napon Izlaza                    | 12/24 V: +/-5 % pri opterećenju<br>14/28 V: bez opterećenja                       |
| Zaštita Od Kratkog Spoja Izlaza | Ugrađena                                                                          |
| Nazivna Snaga U Va              | 63 VA                                                                             |
| Temperature Derating Table      | 63 VA 35 °C<br>59,85 VA 40 °C<br>50,4 VA 50 °C<br>37,8 VA 55 °C<br>28,35 VA 60 °C |
| Način Montiranja                | Fiksno                                                                            |
| Nosači Za Montažu               | 35 mm simetrična DIN šina                                                         |
| 9 Mm Redovi                     | 10                                                                                |
| Visina                          | 89 mm                                                                             |
| Širina                          | 90 mm                                                                             |
| Dubina                          | 60 mm                                                                             |
| Boja                            | Bela                                                                              |
| Pomoćni Priključni Blok         | Tunel kleme 4 mm²                                                                 |

## Okruženje

|                                    |                                           |
|------------------------------------|-------------------------------------------|
| Standardi                          | IEC 61558-2-6<br>EN 60742<br>EN 61558-2-6 |
| Sertifikacija Proizvoda            | NF                                        |
| Kategorija Prenapona               | Klasa II sa poklopcem priključaka opciono |
| Temperatura Okoline Za Rad Uređaja | -20...55 °C                               |

Temperatura Okoline Za Skladištenje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

## Pakovanje

|                              |            |
|------------------------------|------------|
| Unit Type Of Package 1       | PCE        |
| Number Of Units In Package 1 | 1          |
| Package 1 Height             | 7,000 cm   |
| Package 1 Width              | 9,500 cm   |
| Package 1 Length             | 9,500 cm   |
| Package 1 Weight             | 1,332 kg   |
| Unit Type Of Package 2       | S02        |
| Number Of Units In Package 2 | 8          |
| Package 2 Height             | 15,000 cm  |
| Package 2 Width              | 30,000 cm  |
| Package 2 Length             | 40,000 cm  |
| Package 2 Weight             | 10,953 kg  |
| Unit Type Of Package 3       | P12        |
| Number Of Units In Package 3 | 64         |
| Package 3 Height             | 45,000 cm  |
| Package 3 Width              | 80,000 cm  |
| Package 3 Length             | 120,000 cm |
| Package 3 Weight             | 89,728 kg  |

## Ugovorna garancija

|           |           |
|-----------|-----------|
| Garancija | 18 months |
|-----------|-----------|

## Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO<sub>2</sub> proizvodima.

**Vodič za procenu održivosti proizvoda** je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)

## Performanse dobrobiti

|                                                                                                                |                                                                                                                                                                             |
|----------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  Reach Bez Svhc               |                                                                                                                                                                             |
|  Bez Toksičnih Teških Metala  |                                                                                                                                                                             |
|  Bez Žive                     |                                                                                                                                                                             |
|  Informacije O Rohs Izuzecima | <a href="#">Da</a>                                                                                                                                                          |
| <b>Propis Reach</b>                                                                                            | <a href="#">REACH deklaracija</a>                                                                                                                                           |
| <b>Eu Rohs Direktiva</b>                                                                                       | Usaglašeno<br><a href="#">EU RoHS deklaracija</a>                                                                                                                           |
| <b>Rohs Regulatorna Za Kinu</b>                                                                                | <a href="#">RoHS deklaracija za Kinu</a><br>Proaktivna RoHS deklaracija za Kinu (izvan RoHS pravnog okvira za Kinu)                                                         |
| <b>Weee</b>                                                                                                    | Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke. |