

Lista sa podacima o proizvodima

Specifikacije



dvostruki naizmenični prekidač,
bez vijaka, bez rama, aluminijum

EPH0600161

Osnovne informacije

Seriya	Asfora
Tip Proizvoda Ili Komponente	Prekidač
Prezentacija Uređaja	Mehanizam sa montažnim ramom
Broj Prekidača	2
Funkcija Prekidača	Jednopolni naizmenični
Tip Opterećenja	Opterećenje za štedljive svetiljke sa balastom: 100 W
Nijansa Boje	Aluminijum
Tip Pakovanja	Pakovanje u kesicama

Dopunske informacije

Montaža Uređaja	Ugradno
Opseg Snage	2300 W
Nazivna Struja	10 AX pri 250 V AC
Broj Kablova	2 kabl(ovi) 2,5 mm²
Krutost Kabla	Fleksibilni Kruti Jednožični višezični
Dužina Ogoljenog Dela Žice	13,0 mm
Materijal	ABS (akrilonitril-butadien-stiren)
Završna Obrada	Ofarban
Provodni Materijal	Bakar
Način Fiksiranja	Zavrtnji ili kukice51...70 mm
Povezivanje - Priklučci	Priklučci bez zavrtnjeva
Širina	71 mm
Visina	71 mm
Dubina	43,0 mm
Projektovana Dubina	15 mm
Masa Proizvoda	0,0621 kg

Okruženje

Standardi	IEC 60669-1
Sertifikacija Proizvoda	TSE VDE

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Oznake Kvaliteta	CE UKR
Ip Stepen Zaštite	IP20
Temperatura Okoline Za Rad Uređaja	-5...40 °C

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5,0 cm
Package 1 Width	7,1 cm
Package 1 Length	16,0 cm
Package 1 Weight	82,0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9,4 cm
Package 2 Width	18,5 cm
Package 2 Length	27,5 cm
Package 2 Weight	852,0 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30,0 cm
Package 3 Width	40,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	10,927 kg

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti



Informacije O Rohs Izuzecima

Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Usaglašeno EU RoHS deklaracija
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu Proaktivna RoHS deklaracija za Kinu (izvan RoHS pravnog okvira za Kinu)
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Nema potrebe za namenskim operacijama recikliranja