



куповина

APC
 GVMDFW-KIT

Overview

Description	Replacement dust filters for wide UPS cabinet.
Model Name	Galaxy VM Dust Filter Kit Wide Power Cabinet
Includes	Installation guide
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Andorra , United Arab Emirates , Afghanistan , Antigua And Barbuda , Anguilla , Albania , Armenia , Netherlands Antilles , Angola , Argentina , Austria , Australia , Aruba , Azerbaijan , Bosnia And Herzegovina , Barbados , Bangladesh , Belgium , Burkina Faso , Bulgaria , Bahrain , Burundi , Benin , Bermuda , Brunei Darussalam , Bolivia , Brazil , Bahamas , Bhutan , Botswana , Belarus , Belize , Canada , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Central African Republic , Congo , Switzerland , Cote D'Ivoire , Cook Islands , Chile , Cameroon , China , Colombia , Costa Rica , Serbia And Montenegro , Cuba , Cyprus , Czech Republic , Germany , Djibouti , Denmark , Dominica , Dominican Republic , Algeria , Ecuador , Estonia , Egypt , Western Sahara , Spain , Ethiopia , Finland , Fiji , Falkland Islands (Malvinas) , France , Gabon , United Kingdom , Grenada , Georgia , French Guiana , Ghana , Gibraltar , Gambia , Guinea , Guadeloupe , Equatorial Guinea , Greece , Guatemala , Guyana , Hong Kong , Honduras , Croatia , Haiti , Hungary , Indonesia , Ireland , Israel , India , Iraq , Iran (Islamic Republic Of) , Iceland , Italy , Jamaica , Jordan , Kenya , Cambodia , SAINT KITTS AND NEVIS , KOREA, REPUBLIC OF , Kuwait , Cayman Islands , Kazakhstan , Lebanon , SAINT LUCIA , Liechtenstein , Sri Lanka , Liberia , Lesotho , Lithuania , Luxembourg , Latvia , Morocco , Moldova, Republic Of , Madagascar , Macedonia , Mali , Myanmar , Martinique , Mauritania , Malta , Mauritius , Malawi , Mexico , Malaysia , Mozambique , Namibia , Niger , Nigeria , Nicaragua , Netherlands , Norway , Nepal , New Zealand , Oman , Panama , Peru , Papua New Guinea , Philippines , Pakistan , Poland , Puerto Rico , Portugal , Paraguay , Qatar , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Sudan , Sweden , Singapore , Slovenia , Slovakia (Slovak Republic) , Sierra Leone , Senegal , Somalia , El Salvador , Turks And Caicos Islands , Chad , Togo , Thailand , Turkmenistan , Tunisia , East Timor , Turkey , Trinidad And Tobago , Taiwan , TANZANIA, UNITED REPUBLIC OF , Ukraine , Uganda , United States , Uruguay , Uzbekistan , SAINT VINCENT AND THE GRENADINES , Venezuela , VIRGIN ISLANDS (UNITED STATES) , Viet Nam , Yemen , Mayotte , South Africa , Zambia , Zimbabwe

Physical

Net Weight 2 kg

Maximum Height	120 mm
Maximum Width	390 mm
Maximum Depth	240 mm
Shipping Weight	3.5 kg
Shipping Height	127 mm
Shipping Width	396 mm
Shipping Depth	241 mm
Color	Light grey

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-999,9 meters
Storage Temperature	-25 - 55 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-14763,6 meters

Conformance

Approvals	C-tick , CE , EN/IEC 62040-1 , EN/IEC 62040-2 , EN/IEC 62040-3 , FCC Part 15 Class A , IBC 2012 and CBC2013 to Sds=2.02g , UL 1778 , VFI-SS-111
Standard warranty	1 year (parts only)