

Lista sa podacima o proizvodima

Specifikacije



strujni transformator tropikalizovani
DIN šina 100/5 za kablove d. 21

METSECT5CC010

Cena* bez PDV-a: 5.143,00 RSD

Osnovne informacije

Grupa Proizvoda	PowerLogic
Ime Proizvoda	CT
Tip Proizvoda Ili Komponente	Strujni transformator
Sekundarna Struja	5 A
Klasa Tačnosti	Klasa 0.5 pri 2 VA Klasa 1 pri 2,5 VA Klasa 3 pri 3,5 VA
[In] Nazivna Struja	100 A

Dopunske informacije

Tip Strujnog Transformatora	Tropikalizacija za kabl
Odnos Strujnog Transformatora	100/5
[Ith] Dozvoljena Termička Struja U Vazduhu	6 kA
Dinamička Podnosiva Struja	2.5 Ith
Maksimalni Faktor Sigurnosti	5
[Ue] Nazivni Napon	< 720 V AC 50/60 Hz
[Ui] Nazivni Napon Izolacije	3 kV
Način Montiranja	Zavrtnjima Sistemom na klik
Nosači Za Montažu	Montažna ploča DIN šina
Širina	44 mm spoljašnja strana:
Visina	65 mm spoljašnja strana:
Dubina	30 mm ram: 37 mm ukupno:
Prečnik	21 mm
Masa Proizvoda	0,19 kg
[Uimp] Nazivni Podnosivi Impulsni Napon	3 kV
Električna Klasa Izolacije	Klasa B
Spoljašnji Prečnik Kabla	21 mm
Pečaćenje	Sa

Okruženje

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Standardi	VDE 0414 IEC 61869-2
Sertifikacija Proizvoda	EAC CE
Ip Stepen Zaštite	IP20
Relativna Vlažnost	0...95 %
Temperatura Okoline Za Rad Uređaja	-25...60 °C

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5,600 cm
Package 1 Width	5,600 cm
Package 1 Length	8,400 cm
Package 1 Weight	192,000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	9,864 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	400
Package 3 Height	27,500 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	88,800 kg

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



RoHS/REACH

Performanse dobrobiti

✓

Bez Žive

✓

Informacije O Rohs Izuzecima

Da

Sertifikacija i standardi

Propis Reach

[REACH deklaracija](#)

Eu Rohs Direktiva

У складу са изузецима

Rohs Regulativa Za Kinu

[RoHS deklaracija za Kinu](#)

Weee

Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.