

Lista sa podacima o proizvodima

Specifikacije



Mini Pragma dozna - 1 x 8 modula - ugradna

MIP82118

Cena* bez PDV-a: 1.711,00 RSD

Osnovne informacije

Grupa Proizvoda	Resi9
Tip Proizvoda Ili Komponente	Baza
Pribor / Posebna Kategorija	Pribor ormana
Kompatibilnost Grupe Proizvoda	Resi9 Resi9 MP
[In] Nazivna Struja	63 A
Nb Of Horizontal Rows	1
Nb Of 18 Mm Modules Per Row	18
Broj Priklučnih Blokova	1 uzemljenje (zavrtanj) sa 16 izvodi 1 nula (zavrtanj) sa 16 izvodi
Funkcija Priključnog Bloka	Uzemljenje/nula

Dopunske informacije

Montaža Ormana	Ugradna
9 Mm Redovi	2
Ukupan Broj 18 Mm Modula	18
Kablovski Uvod	Predefinisani otvori
Izvodi Razvodnog Bloka	2 x 16 mm ² za uzemljenje 2 x 16 mm ² za nula 6 x 6 mm ² za uzemljenje 6 x 6 mm ² za nula 8 x 10 mm ² za uzemljenje 8 x 10 mm ² za nula
Materijal Kućišta	Zadnji deo: tehno plastika
Širina	378 mm zid:
Visina	228 mm zid:
Dubina	80 mm zid: 18 mm spoljašnja strana: 98 mm ukupno:

Okruženje

Standardi	EN 50102 IEC 60695-2-11
Otpornost Na Vatru	Zadnji deo: 650 °C
Ik Stepen Zaštite	IK07
Temperatura Okoline Za Rad Uređaja	-25...60 °C

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8,000 cm
Package 1 Width	37,800 cm
Package 1 Length	22,800 cm
Package 1 Weight	674,000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	6
Package 2 Height	52,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	4,144 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	96
Package 3 Height	120,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	78,304 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti

- ✓

Bez Žive
- ✓

Informacije O Rohs Izuzecima

Da
- ✓

Proizvod Bez Halogena

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu Proizvod je izvan RoHS okvira za Kinu. Informativna deklaracija supstanci.
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Profil Cirkularnosti	Nema potrebe za namenskim operacijama recikliranja