



Overview

Description	Universal Sensor that monitors access to a rack or room.
Model Name	NetBotz Door Switch Sensor for Rooms or 3rd Party Racks - 50 ft.
Includes	Cable ties
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guatemala , Guinea , Guyana , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Japan , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Mauritania , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

General

Number of Universal Sensor Ports	0
Number of Sensor Pods Supported	0
Number of Universal Sensors Supported	0
Number of Ports	0

Physical

Net Weight	0.19 kg
Maximum Height	25.0 mm
Maximum Width	111.0 mm

Maximum Depth	155.0 mm
Shipping Weight	0.31 kg
Shipping Height	48.0 mm
Shipping Width	232.0 mm
Shipping Depth	164.0 mm
Units per Pallet	0.0

Environmental

Operating Environment	0 - 45 °C
Storage Temperature	-15 - 65 °C
Operating Relative Humidity	0 - 95 %
Storage Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Elevation	0-15000 meters

Conformance

Standard warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs