

Lista sa podacima o proizvodima

Specifikacije



ind.kutije IP66 IK08 RAL7035
U:V105Š105D55 S:V116Š116D62
neprovidan PC pokl. V10

NSYTBP11116

Cena* bez PDV-a: 1.326,00 RSD

Osnovne informacije

Grupa Proizvoda	Thalassa
Ime Proizvoda	Thalassa TBP
Primena Uređaja	Više namena
Category	Industrijska kutija
Visina	116 mm
Širina	116 mm
Dubina	62 mm
Unutrašnja Visina	105 mm
Unutrašnja Širina	105 mm
Unutrašnja Dubina	55 mm
Montaža Ormana	Montaža na zid
Sastav Uređaja	1 telo 1 poklopac 4 zavrtnj poklopca
Količina Po Setu	Set od 5
Tip Kućišta	Izliveno iz jednog dela
Tip Prednjeg Poklopca	Niski puni poklopac
Fiksiranje Poklopca	Plastični zavrtnji
Tip Brave	Neodvojiv zavrtnj ravan spoljašnja zaptivena oblast
Odvojnivi Delovi	Poklopac sa neodvojivim zavrtnjima

Dopunske informacije

Materijal	Polikarbonat
Boja	Siva (RAL 7035)
Standardi	IEC 62208 UL 508 A
Sertifikacija Proizvoda	TÜV UL
Električna Klasa Izolacije	Klasa II
Lokacija Montaže	Na otvorenom (sa nadstrešnicom ili zaklonom i antikondenzacionim ventilom)
Masa Proizvoda	0,171 kg

Okruženje

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Ip Stepen Zaštite	IP66 u skladu sa NEMA 4.4X
Ik Stepen Zaštite	IK08 conforming to IEC 62262
Otpornost Na Vatru	960 °C
Temperatura Okoline Za Skladištenje	-15...60 °C
Operating Temperature	-25...80 °C

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12,2 cm
Package 1 Width	12,0 cm
Package 1 Length	33,0 cm
Package 1 Weight	171,0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12,2 cm
Package 2 Width	12,0 cm
Package 2 Length	33,0 cm
Package 2 Weight	857,0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	75
Package 3 Height	40,0 cm
Package 3 Width	40,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	14,66 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti

- ✓

Reach Bez Svhc
- ✓

Bez Toksičnih Teških Metala
- ✓

Bez Žive
- ✓

Informacije O Rohs Izuzecima

Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu Proaktivna RoHS deklaracija za Kinu (izvan RoHS pravnog okvira za Kinu)
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Profil Cirkularnosti	Informacije o kraju radnog veka