

Product datasheet

Specifications



Mini enclosure for modular device,
Mureva Enclosure, 1x8 modules,
without terminal block

13978

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Mini enclosure for modular device
Mounting Plate Description	Slotted

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	16
Number Of 18 Mm Modules Per Row	8
Total Number Of 18 Mm Modules	8
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 marking kit
Type Of Front Cover	Transparent
Power Dissipation In W	15 W
[In] Rated Current	63 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	5
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	195 mm
Height	200 mm
Depth	112 mm
Internal Depth	56 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Environment

Standards	IEC 60695-2-1 IEC 61439-3 IEC 60670 EN 50262
-----------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11 cm
Package 1 Width	19.4 cm
Package 1 Length	19.6 cm
Package 1 Weight	630 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	21.7 cm
Package 2 Width	34.6 cm
Package 2 Length	40 cm
Package 2 Weight	4.1 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	80 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	113.52 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Lower Impact Materials Transparency RoHS/REACH

Resource performance

✓

Minimum Percentage Of Recycled Plastic Content

24

Well-being performance

✓

Rohs Exemption Information

Yes

✓

Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations