Product datasheet

Specifications





Safety switch, general duty, non fusible, 100A, 3 pole, 3 wire, 30hp, 240VAC, NEMA 3R, bolt on hub provision

DU323RB

Main

Product	Single Throw Safety Switch	
Duty Rating	General duty	
Device Application	Residential	
Disconnect Type	Non-fusible disconnect switch	
Factory Installed Neutral	None	
Phase	3 phases	
Number Of Poles	3	
Current Rating	100 A	
Voltage Rating	240 V AC	
Enclosure Rating Nema	NEMA 3R	
Motor Power Hp	15 hp at 240 V AC 60 Hz for 1 phase motors 30 hp at 240 V AC 60 Hz for 3 phases motors	

Complementary

Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	3-wire	
Wire Size	AWG 14AWG 1 copper AWG 12AWG 1 aluminium	
Tightening Torque	3.95 N.m for 2.085.26 mm² (AWG 14AWG 10)	
	3.95 N.m (AWG 14AWG 10) 4.52 N.m for 8.37 mm² (AWG 8)	
	5.08 N.m for 12.321.12 mm² (AWG 6AWG 4) 5.65 N.m (AWG 3AWG 1)	
Depth	165.10 mm	
Width	266.70 mm	
Height	444.50 mm	
Net Weight	7 kg	

Environment

Certifications UL listed file E2875

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	18.542 cm
Package 1 Width	26.67 cm
Package 1 Length	50.546 cm
Package 1 Weight	6.704 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	40
Package 2 Height	101.6 cm
Package 2 Width	101.6 cm
Package 2 Length	121.92 cm
Package 2 Weight	286.67 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations