


Product datasheet

Specifications

Category 3 25 pair UTP Cable 305m



DXYCAT3UT25P

⚠ Discontinued on: Jan 23, 2021 AD

⚠ Discontinued

Main

Product Or Component Type	Copper cable
Cable Shielding Type	UTP
Communication Network Category	3
Colour Tint	Grey

Complementary

Type Of Cable	25 pairs cable
Nominal Velocity Propagation	69 %
Capacitance Unbalance	3.28 pF / 1 m
Cable Outer Diameter	11 mm
Cable Length	305 m
Awg Gauge	AWG 24
Thickness	Insulation: 0.2 mm Jacket: 1.1 mm
Pulling Force	40 N
Material	PVC (polyvinyl chloride): jacket

Environment

Standards	ISO/IEC 11801 ANSI/TIA-568-A
-----------	---------------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Under investigation	
China Rohs Regulation	China RoHS declaration	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	