

# Product datasheet

Specifications



## Pieno - 16A 250V - 3 gang 2 way switch with fluorescent locator (MB)

E8233L2F\_MB

### Main

Range of product	Pieno
Product or component type	Switch
Switch function	2-way
Switch application	Switch
Rated current	16 AX at 250 V AC 50 Hz
Local signalling	Fluorescent (white)
Number of gangs	3 gangs
Load type	Resistive Fluorescent

### Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	Pillar terminals
Clamping connection capacity	2 x 1.5 mm <sup>2</sup> for stranded cable(s) 2 x 2.5 mm <sup>2</sup> for solid cable(s)
Width	87 mm
Height	87 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 60669-1 GB 16915.1
Product certifications	CCC

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm

Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	97.7 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)