

Product datasheet

Specifications



Safety switch, heavy duty, non fusible, 60A, 3 wire, 3 poles, 60hp, 600VAC/DC, Type 3R, bolt on hub provision

HU362RB

Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Network number of phases	3 phases
Number of Poles	3
Current Rating	60 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R galvanized steel
Motor power hp	10 hp at 240 V AC 50...60 Hz for 1 phase motors 20 hp at 240 V AC 50...60 Hz for 3 phases motors 25 hp at 480 V AC 50...60 Hz for 1 phase motors 50 hp at 480 V AC 50...60 Hz for 3 phases motors 30 hp at 600 V AC 50...60 Hz for 1 phase motors 60 hp at 600 V AC 50...60 Hz for 3 phases motors 10 hp at 250 V DC 30 hp at 600 V DC

Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring configuration	3-wire
Wire Size	AWG 14...AWG 3 copper AWG 12...AWG 3 aluminium
Tightening torque	5.65 N.m (AWG 3) 5.08 N.m (AWG 6...AWG 4) 4.52 N.m for 8.367 mm ² (AWG 8) 5.65 N.m for 2.06...5.261 mm ² (AWG 14...AWG 10)
Depth	162.05 mm
Width	266.70 mm
Height	539.75 mm
Net weight	7 kg

Environment

Certifications	UL listed file E2875
----------------	----------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.828 cm
Package 1 Width	29.972 cm
Package 1 Length	50.546 cm
Package 1 Weight	6.895 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	40
Package 2 Height	115.57 cm
Package 2 Width	101.6 cm
Package 2 Length	121.92 cm
Package 2 Weight	293.02 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)