# **Product datasheet**

Specification





# Acti 9 ID K - residual current circuit breaker - 4P - 63A - 300mA - type AC

A9KR16463

## Main

Range	Acti9
Product Name	Acti9 ID K
Product Or Component Type	Residual current circuit breaker (RCCB)
Device Short Name	ID K
Poles Description	4P
Neutral Position	Left
[In] Rated Current	63 A
Network Type	AC
Earth-Leakage Sensitivity	300 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Type AC

## Complementary

Complementary	
Device Location In System	Group incomer
Network Frequency	50 Hz
[Ue] Rated Operational Voltage	380415 V AC 50 Hz
Residual Current Tripping Technology	Voltage independent
Rated Breaking And Making Capacity	Idm 630 A Im 630 A
Rated Conditional Short-Circuit Current	GL63: Inc 4.5 kA K60: Inc 6 kA
[Ui] Rated Insulation Voltage	440 V AC 50 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Contact Position Indicator	No
Control Type	Toggle
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	8
Height	81 mm
Width	72 mm
Depth	68 mm
Net Weight	0.35 kg

Colour	White	
Mechanical Durability	5000 cycles	
Electrical Durability	AC-1: 4000 cycles	
Connections - Terminals	Biconnect top or bottom 135 mm² rigid Biconnect top or bottom 125 mm² flexible	
Wire Stripping Length	14 mm for top or bottom connection	
Tightening Torque	3.5 N.m top or bottom	

# **Environment**

Standards	EN/IEC 61008-1
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	2
Electromagnetic Compatibility	8/20 μs impulse withstand, 200 A conforming to EN/IEC 61008-1
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-555 °C
Ambient Air Temperature For Storage	-2585 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	8.0 cm
Package 1 Length	9.0 cm
Package 1 Weight	0.446 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	27
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	16.056 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations