

Product datasheet

Specifications



Fluid Cooler 57MBH@25 TD,
10GPM, 5Feeds, 400/3/50

ACFC75256

Overview

Lead TimeSpecial Order - Call for Quoted Lead Times

Main

Main Input Voltage380 V 3 phases
400 V 3 phases
415 V 3 phases

Provided EquipmentInstallation guide

General

Air Flow4223.93 l/s

Physical

Height98 cm

Width90 cm

Depth191 cm

Net Weight90 kg

Mounting PreferenceNo preference

Mounting ModeNot rack-mountable

Input

Network Frequency50 Hz

Conformance

Product CertificationsTÜV

Packing Units

Unit Type Of Package 1PCE

Number Of Units In Package 11

Package 1 Height152.4 cm

Package 1 Width248.9 cm

Package 1 Length152.4 cm

Package 1 Weight170 kg

Number Of Units In Package 31

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not compliant
