Product datasheet

Specification





VarPlus Box HDuty Capacitor - 20.8/25 kvar - 400 V - 50/60Hz

BLRBH208A250B40

! Discontinued on: 1 Nov 2020

(!) Discontinued

Main

Range Of Product	VarPlus Box
Product Or Component Type	Heavy duty capacitor
Network Frequency	50/60 Hz
Series Name	HDuty
Network Harmonic Content	<= 20 %
Electrical Parameters	18.8 kvar 380 V 50 Hz
	22.6 kvar 380 V 60 Hz
	20.8 kvar 400 V 50 Hz
	25 kvar 400 V 60 Hz
	22.4 kvar 415 V 50 Hz
	26.9 kvar 415 V 60 Hz
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours)
Continuous Overcurrent Capacity	1.8 x ln
Rated Voltage	380 415 V AC 50/60 Hz

Complementary

Dielectric Losses	< 0.2 W/kvar	
Power Losses	< 0.5 W/kVAr	
Capacitance Tolerance	- 5 % to 10 %	
Voltage Test	2.15 x Un AC between terminals for 10 s <= 660 V - 3 kV AC between terminal and container for 10 s >= 660 V - 6 kV AC between terminal and container for 10 s	
Inrush Current	250 x ln	
Maximum Switching Operation Per Year	7000	
Service Life In Hours	130000 h	
Dielectric Material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)	
Impregnation Material	Non-PCB dry PUR resin Biodegradable	
Type Of Installation	stallation Indoor installation	
Connections - Terminals	M8 stud with bushing terminal	
Mounting Mode	Upright	
Height	355 mm	
Width	309 mm	

Depth	153 mm	
Net Weight	7.5 kg	

Environment

Standards	IEC 60831-2 IEC 60831-1
Ip Degree Of Protection	IP20
Operating Altitude	2000 m
Temperature Class	D
Ambient Air Temperature For Operation	-2555 °C
Relative Humidity	95 %

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information