Product datasheet

Specification





Fuse carrier, TeSys DF, 3P+N, 125A, 690VAC, fuse size 22x58mm, with tubular link

DF223NC

Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF22
Device Composition	tubular link for locked in Neutral pole
Product Compatibility	DF3FA fuse cartridge striker DF3FN fuse cartridge striker DF22AM auxiliary contact block
Poles Description	3P + N
Fuse Size	22 x 58 mm
Fuse Type	, gG , aM
Control Type	Toggle
[Ue] Rated Operational Voltage	690 V AC 690 V DC
[le] Rated Operational Current	125 A
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[lpk] Rated Peak Withstand Current	19 kA with tubular links conforming to IEC 60269-1
Short-Circuit Withstand	120 kA 400 V conforming to IEC 60947-3 120 kA 500 V conforming to IEC 60947-3 80 kA 690 V conforming to IEC 60947-3

Complementary

Standards	EN/IEC 60947-3
	EN/IEC 60269-2
	UL 4248-1
	CSA C22.2 No 4248-1
Product Certifications	IEC
	UL recognized
	CSA
	EAC
Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical (tolerance: +/- 23°)
Connections - Terminals	Screw clamp terminals 1 cable(s) 2.535 mm²rigid
	Screw clamp terminals 2 cable(s) 2.525 mm²rigid
	Screw clamp terminals 1 cable(s) 2.535 mm²flexible with or without
	Screw clamp terminals 2 cable(s) 2.525 mm²flexible with or without
	Colow clamp terminals 2 capic(s) 2.525 mm nexible with or without

25 Apr 2024 Life Is On Schneider

Tightening Torque	4 N.m
Height	127.5 mm
Width	140 mm
Depth	76.5 mm
Net Weight	0.892 kg
Quantity Per Set	Set of 1

Environment

Ambient Air Temperature For Storage	-4080 °C
Ambient Air Temperature For Operation	-2060 °C with derating above 20°C
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	TH
Fire Resistance	960 °C conforming to IEC 60695-2-1
Compatibility Code	DF22

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	13.5 cm
Package 1 Length	23.2 cm
Package 1 Weight	824.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	9
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.86 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
	Circularity Profile