# **Product datasheet**





# S-Classic - bell press switch - 1 gang - white

E31\_1RBPRPA\_WE

! Discontinued on: 30 Jun 2023

#### Main

Range	S-Classic
Product Or Component Type	Bell press switch
Switch Application	Bell switch
Quantity Per Set	Set of 1

### **Complementary**

Control Type	Push-button
Actuator	Push-button
Number Of Gangs	1 gang
Device Mounting	Surface Flush
Rated Current	10 AX at 250 V AC
Material	Plate: PC (polycarbonate), white Dolly: PC (polycarbonate), white Base: PA66, black
Embedding Depth	12.3 mm
Height	87 mm
Width	87 mm
Depth	28.9 mm

#### **Environment**

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	MS IEC 60669-1 IEC 60669-1

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	55 g

Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	14.8 cm
Package 2 Width	18 cm
Package 2 Length	10 cm
Package 2 Weight	622 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	20.3 cm
Package 3 Width	47.3 cm
Package 3 Length	30.5 cm
Package 3 Weight	7430 g



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations