

Product datasheet

Specifications



10A INTERNATIONAL SOCKET, WHITE

E3426_10IS_WW

Main

Range	Neo
Product or component type	Power socket-outlet
Device application	Power supply
Outlet poles configuration	3P with shutters 2P with shutters
Outlet standard	IEC 60884
Colour tint	White

Complementary

Wiring device mounting	Flush Surface
Rated current	10 A at 250 V AC 50/60 Hz
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Load type	Resistive
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	23 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	95.0 g
Package 1 Height	2.3 cm

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	3200
Package 2 Weight	357600.0 g
Package 2 Height	1400.0 mm
Package 2 Width	1140.0 mm
Package 2 Length	1140.0 mm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	774.0 g
Package 3 Height	15.0 cm
Package 3 Width	19.0 cm
Package 3 Length	8.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)