

Product datasheet

Specifications



Pieno - 10A 250V - 1 G bell sw w "Privacy"&"Please Clean Up" &"Please Wait" (MB)

E8231BPDMW_MB

Main

Range of product	Pieno
Product or component type	Switch
Switch function	Switch
Switch application	Bell switch
Rated current	10 A at 250 V AC 50 Hz
Local signalling	Please wait, neon (orange) Please clean up, neon (green) Privacy, neon (red)
Load type	Resistive Fluorescent

Complementary

Wiring device mounting	Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	By screw
Clamping connection capacity	1 x 2.5 mm ² for solid cable(s) 1 x 1.5 mm ² for stranded cable(s)
Embedding depth	21 mm
Width	87 mm
Height	87 mm
Depth	35.5 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	GB 16915.1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.57 cm

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	111.17 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)