


# Product datasheet

Specifications



## 10A Mechanical Curtain Switch with Fluorescent Locator, White

E8231CF\_WE

 **Discontinued on:** 1 Nov 2020

 **Discontinued**

### Main

Range	Pieno
Product Or Component Type	Switch
Switch Application	Curtain switch
Load Type	Resistive Fluorescent
Cover Frame Colour Tint	White

### Complementary

Device Mounting	Flush Surface
Wiring Device Mounting	Flush Surface
Switch Function	Switch
Rated Current	10 A at 250 V AC 50 Hz
Local Signalling	Fluorescent (white)
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	2 x 1.5 mm <sup>2</sup> for stranded cable(s) 1 x 2.5 mm <sup>2</sup> for solid cable(s)
Embedding Depth	22.6 mm
Width	87 mm
Height	87 mm
Depth	22.6 mm

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS EN 60669-1 MS IEC 60669-1 IEC 60669-1 GB 16915.1

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	98.58 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	591.48 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	32.5 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	5914.8 g

## Contractual warranty

Warranty	18 months
----------	-----------