

# Product datasheet

Specifications



## Pieno - 16A 250V - electronic key card switch with time delay (MB)

E8231EKT\_MB

### Main

Product or component type	Electronic keycard reader
Rated current	16 A at 220...240 V AC 50/60 Hz
Load type	Resistive

### Complementary

Material	Polycarbonate: surround Polycarbonate: grid plate
Wiring device mounting	Flush
Width	87 mm
Height	87 mm
Depth	9.1 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Standards	IEC 60669-2-1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	135 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>

<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

**Recommended replacement(s)**