# **Product datasheet**

Specifications





# 16AX 250V 2 Gang 2 Way Switch with Fluorescent Locator, White

E8232L2F\_WE

#### Main

Range	Pieno
Product Or Component Type	Switch
Switch Application	Switch
Load Type	Fluorescent Resistive
Cover Frame Colour Tint	White

### Complementary

Complementary	
Device Mounting	Flush Surface
Wiring Device Mounting	Flush Surface
Switch Function	2-way
Rated Current	16 AX at 250 V AC 50 Hz
Local Signalling	Fluorescent (white)
Number Of Gangs	2 gangs
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	2 x 1.5 mm <sup>2</sup> for stranded cable(s) 2 x 2.5 mm <sup>2</sup> for solid cable(s)
Embedding Depth	23 mm
Width	87 mm
Height	87 mm
Depth	23 mm

#### Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	IEC 60669-1
	GB 16915.1
	BS EN 60669-1
	MS IEC 60669-1
	SS 227-1

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	797 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	7973.6 g

## **Contractual warranty**

Warranty

18 months

Life Is On Schneider

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations