

Product datasheet

Specifications



Pieno - 10A 250V - 4 gang 1 way switch with fluorescent locator (MB)

E8234L1F_MB

Main

Range of product	Pieno
Product or component type	Switch
Switch function	1-way
Switch application	Switch
Rated current	10 AX at 250 V AC 50 Hz
Local signalling	Fluorescent (white)
Number of gangs	4 gangs
Load type	Fluorescent Resistive

Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	Pillar terminals
Clamping connection capacity	2 x 1.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s)
Width	87 mm
Height	87 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 60669-1 GB 16915.1
Product certifications	CCC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm

Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	102.8 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.124 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	7.224 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)