

Product datasheet

Specifications



Powex socket-outlet extension - surge protection+2 USB ports - 3 gangs - 13 A

EPB4PBS

⚠ Discontinued on: 1 Nov 2020

⚠ Discontinued

Main

Range Of Product	Powex
Product Or Component Type	Service box
Device Presentation	Pre-wired, with outlets, cable and plug
Colour Tint	White

Complementary

Number Of Gangs	3 gangs
Number Of Power Socket Outlets	3 x 2P + E with shutters, United Kingdom
Integrated Connection Type	USB port, output voltage= 5 V DC at 1 A USB port, output voltage= 5 V DC at 2.1 A
Control Type	Switch for socket-outlet with LED
Type Of Cable	A05 VVF 2 m 1.25 mm²
[Ue] Rated Operational Voltage	250 V AC at 13 A
Protection Type	Output surge protection Overload protection Inrush surge protection
Energy Peak	1650 J
Surge Current	30000 A
Surge Withstand	1200 V
Response Time	< 1 ns
Local Signalling	LED (green) for surge arrester indication LED (red) for insulation fault
Material	Phosphor bronze: connections PC: housing Galvanised steel: screw
Surface Finish	Silkscreened

Environment

Standards	IEC 61058 BS 1363-2 IEC 60884-2-5 EN 60950-1 EN 61643-11 IEC 60884-1
Ambient Air Temperature For Operation	0...45 °C
Ambient Air Temperature For Storage	0...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	10...95 % non-condensing
-------------------	--------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	18 cm
Package 1 Length	44.4 cm
Package 1 Weight	900 g