

Product datasheet

Specifications



Double pole switch with neon, 20AX, 250V

ESM32D20NA

Main

Range	S-Classic
Product or component type	Switch
Device application	Control

Complementary

Control type	Rocker
Actuator	Rocker
Pilot light	neon indicator
Device mounting	Surface Flush
Rated current	20 A at 250 V AC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	8.1 cm
Package 1 Length	8.1 cm
Package 1 Weight	280.5 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	25.7 cm
Package 2 Width	8.7 cm
Package 2 Length	5 cm
Package 2 Weight	1.403 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	18.2 cm
Package 3 Width	44 cm
Package 3 Length	27 cm

Package 3 Weight 14.365 kg

Offer Sustainability

Sustainable offer status Green Premium product

REACH Regulation [REACH Declaration](#)

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Mercury free Yes

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

RoHS exemption information Yes

Environmental Disclosure [Product Environmental Profile](#)

Recommended replacement(s)