Product datasheet

Specifications





circuit breaker, EasyPact EZC100B, TMD, 15A, 3 poles 3d

EZC100B3015

Main

EasyPact
Circuit breaker
Easypact EZC100B
Easypact EZC100B
Distribution
3P
3t
DC AC
50/60 Hz
15 A at 40 °C
690 V AC 50/60 Hz conforming to IEC 60947-2
6 kV conforming to IEC 60947-2
550 V AC 50/60 Hz conforming to IEC 60947-2
В
10 kA lcu at 110130 V AC 50/60 Hz conforming to IEC 60947-2 10 kA lcu at 220240 V AC 50/60 Hz conforming to IEC 60947-2 5 kA lcu at 440 V AC 50/60 Hz conforming to IEC 60947-2 2.5 kA lcu at 550 V AC 50/60 Hz conforming to IEC 60947-2 7.5 kA lcu at 380 V AC 50/60 Hz conforming to IEC 60947-2 7.5 kA lcu at 440415 V AC 50/60 Hz conforming to IEC 60947-2
0.625 kA at 550 V AC 50/60 Hz conforming to IEC 60947-2 1.25 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 1.875 kA at 380 V AC 50/60 Hz conforming to IEC 60947-2 1.875 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 2.5 kA at 110/130 V AC 50/60 Hz conforming to IEC 60947-2 2.5 kA at 220/230/240 V AC 50/60 Hz conforming to IEC 60947-2
Yes conforming to IEC 60947-2
Category A
TM-D
Thermal-magnetic
15 A at 50 °C
Overload protection
Short-circuit protection

Complementary

· · · · · · · · · · · · · · · · · ·		
Control Type	Toggle	
Mounting Mode	Fixed	
Mounting Support	Backplate	
Upside Connection	Front	
Downside Connection	Front	
Mechanical Durability	8500 cycles	
Electrical Durability	Category A: 1500 cycles 415 V AC 50/60 Hz conforming to IEC 60947-2	
Connection Pitch	25 mm	
Local Signalling	Positive contact indication	
Neutral Protection Setting	Without protection	
Earth-Leakage Protection	Without	
Height	130 mm	
Width	75 mm	
Depth	60 mm	

Environment

Standards	EN/IEC 60947-2 JIS C8201-2-2 EN/IEC 60947-1 GB/T 14048.2	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ik Degree Of Protection	IK07 conforming to IEC 62262	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-3585 °C	

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	14.0 cm
Package 1 Length	8.5 cm
Package 1 Weight	826.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	12
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	13.3 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	24
Package 3 Height	30.0 cm

Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	20.311 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Dimensions Drawings



Assembly



Performance Curves

