

# Product datasheet

Specifications



## 1 Gang 250VA Fan Speed Controller

KB31RF250\_WE

⚠ Discontinued

### Main

Range	Vivace
Device short name	KB31
Product or component type	Speed controller
Device application	Control
Device presentation	Complete mechanism
Colour tint	White

### Complementary

Power range	Motor: 250 VA
[Ue] rated operational voltage	220...240 V AC
Network frequency	50 Hz
Number of gangs	1 gang
Connections - terminals	Pillar terminals
Terminal identifier	L Load
Tightening torque	0.4 N.m
Clamping connection capacity	1.5 mm <sup>2</sup>
Contacts material	Brass and phosphor bronze
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Width	87 mm
Height	87 mm
Projecting depth	8 mm
Embedding depth	35 mm

## Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	9 cm
Package 1 Length	9 cm
Package 1 Weight	96 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	894 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	9716 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	<a href="#">Yes</a>

## Recommended replacement(s)