# **Product datasheet**

Specifications





# Vivace-one way switch 16 AX 250V-1 module -White

KB34S\_1\_WE\_G2

### Main

Range	Vivace
Product Or Component Type	Switch
Device Short Name	KB34
Device Application	Lighting
Switch Function	1-way

## Complementary

Complementary	
Device Presentation	Complete mechanism
Actuator	Rocker
Number Of Gangs	4 gangs
Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base Polycarbonate: dolly Nylon: actuator Silver plated copper: bridge Brass: terminal cover
Surface Finish	Glossy
Surface Treatment	Untreated
Type Of Packing	Box
Quantity Per Set	8
Sale Per Indivisible Quantity	1
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Embedding Depth	24 mm
Rated Current	10 AX at 250 V AC, inductive 10 A at 250 V AC, resistive
[Ue] Rated Operational Voltage	250 V AC
Network Frequency	50 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	8 screw terminals

Terminal Identifier	COM L1
	L2
Tightening Torque	0.4 N.m
Clamping Connection Capacity	<= 2 x 2.5 mm² for rigid or stranded cable(s)
Wire Stripping Length	12 mm
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un
Width	86 mm
Height	86 mm
Depth	36.5 mm
Net Weight	0.0829 kg

## **Environment**

Standards	IEC 60669
Product Certifications	SNI SIRIM
Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	2.4 cm
Package 1 Length	8.6 cm
Package 1 Weight	85 g



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations