


Product datasheet

Specifications



Vivace-one way switch 16 AX 250V-1 module -White

KB34S_1_WE_G2

Main

Range	Vivace
Product or component type	Switch
Device short name	KB34
Device application	Lighting
Device presentation	Complete mechanism

Complementary

Switch function	1-way
Actuator	Rocker
Number of gangs	4 gangs
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base Polycarbonate: dolly Nylon: actuator Silver plated copper: bridge Brass: terminal cover
Surface finish	Glossy
Surface treatment	Untreated
Type of packing	Box
Quantity per set	8
Sale per indivisible quantity	1
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Embedding depth	24 mm
Rated current	10 AX at 250 V AC, inductive 10 AX at 250 V AC, resistive
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze

Connections - terminals	8 screw terminals
Terminal identifier	COM L1 L2
Tightening torque	0.4 N.m
Clamping connection capacity	<= 2 x 2.5 mm ² for rigid or stranded cable(s)
Wire stripping length	12 mm
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 I _n and 1.1 I _{un}
Width	86 mm
Height	86 mm
Depth	36.5 mm
Net weight	0.0829 kg

Environment

Standards	IEC 60669
Product certifications	SNI SIRIM
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	2.4 cm
Package 1 Length	8.6 cm
Package 1 Weight	85 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	740 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	7050 g

Offer Sustainability

Sustainable offer status	Green Premium product
---------------------------------	-----------------------

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)