


Product datasheet

Specifications



Contactor coil,Easy TeSys Control, 48V AC,50Hz,spare part for LC1E06...E18

LAEX1E5

 **Discontinued on:** 1 Nov 2020

 **Discontinued**

Main

Range	Easy TeSys
Range Of Product	Easy TeSys Control
Product Or Component Type	Contactor coil
Device Short Name	LAEX
Product Compatibility	LC1E06...E18
Control Circuit Type	AC at 50 Hz standard
[Uc] Control Circuit Voltage	48 V AC 50 Hz
Average Resistance	37 Ohm at 20 °C
Inductance Of Closed Circuit	1.32 H

Complementary

Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc at 50 Hz (at <55 °C)
Inrush Power In Va	95 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	8.5 VA 50 Hz cos phi 0.3 (at 20 °C)

Environment

Ambient Air Temperature For Operation	-5...55 °C
Net Weight	0.056 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)
