

# Product datasheet

Specifications



## 1 Gang Telephone/Data Socket Module

US31RJ\_000

### Main

Range	Ulti
Product Or Component Type	Data/telephone socket module
Number Of Gangs	1 gang
Data Socket Type	RJ45

### Complementary

Wiring Device Mounting	Surface Flush
Fixing Mode	By screws
Distance Between Centers	60.3 mm
Width	87 mm
Height	87 mm
Depth	13.1 mm

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications