

Product datasheet

Specifications



2 Gang Telephone and Data Socket Module

US32TD_000

Main

Range	Ulti
Product Or Component Type	Data/telephone socket module
Number Of Gangs	2 gangs
Data Socket Type	RJ45

Complementary

Wiring Device Mounting	Flush Surface
Fixing Mode	By screws
Distance Between Centers	60.3 mm
Width	87 mm
Height	87 mm
Depth	13.1 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications