

Product datasheet

Specifications



Universal Shaver Socket, 100/240VAC, Crystal Glass

US727H_XGL

⚠ Discontinued on: 12 Jan 2023

⚠ End-of-service on: 9 Nov 2023

⚠ Discontinued

Main

Product Or Component Type	Shaver socket
Number Of Gangs	1 gang
Rated Current	20 A at 240 V AC 50 Hz

Complementary

Load Type	115 V AC 240 V AC
Number Of Cables	1 cable(s) 2.5 mm ²
Fixing Mode	By screws
Wiring Device Mounting	Surface Flush
Distance Between Centers	120.6 mm
Width	87 mm
Height	147 mm
Depth	45 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m
Standards	IEC 61558-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	14.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	804.95 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	16.3 cm
Package 2 Width	33 cm
Package 2 Length	50.4 cm
Package 2 Weight	16099 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	400
Package 3 Height	86 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	321980 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation